

FLUID ASPIRATION

RELIABLE VACUUM WITH PROCESS-SPECIFIC FLOW RATES



LABOPORT®



SMALL AND FOR (ALMOST) ANY USE

N 96 Mini Diaphragm Vacuum Pump

- Flow rate 0.4 m³/h / Ultimate vacuum < 130 mbar abs.
- Extremely low footprint
- Integrated rotational speed control
- PTFE-coated diaphragm is ideal for aggressive/corrosive gases and vapors

LABOPORT®



HIGH-PERFORMANCE

N 816.3 KT.18 Diaphragm Vacuum Pump

- Flow rate 0.96 m³/h / Ultimate vacuum 20 mbar abs.
- PTFE-coated diaphragm is ideal for aggressive/corrosive gases and vapors

LABOPORT®



FAST

N 938.50 KT.18 Diaphragm Vacuum Pump

- Flow rate 1.8 m³/h / Ultimate vacuum 15 mbar abs.
- Connecting both pump heads in parallel and in series ensures exceptionally fast evacuation
- PTFE-coated diaphragm is ideal for aggressive/corrosive gases and vapors

LABOPORT®



CHEMICALLY RESISTANT

N 820 G Diaphragm Vacuum Pump

- Flow rate 1.2 m³/h / Ultimate vacuum 6 mbar abs.
- High level of vapor and condensate compatibility
- Integrated rotational speed control
- PTFE pump head combined with PTFE-coated diaphragm are ideal for extremely aggressive/corrosive gases and vapors
- ATEX-compliant in accordance with **Ex II 2/-G IIB+H2 T3 internal atmosphere only**
- Integrated gas ballast valve
- 3-color status display for in operation / stand-by / error
- High suction speed, particularly in the low vacuum range

Tip: When combined with the VC 900 vacuum control unit and the connection cable, the rotational speed is controlled in accordance with the requirements of the process. Ideal for combining with all common vacuum controllers with valve control.